

PHILIPS

Patient monitoring

Efficia patient monitors

Efficia patient monitor product structure

✓ Standard ● Optional



Model

6NC number

Monitor

CM10

863301

10" (A)

CM12

863303

12" (A)

CM100

863300

10"

CM120

863302

12"

CM150

863304

15"

Features

Patient data to USB (csv)

✓

✓

✓

✓

✓

External slave display connection

✓

✓

✓

✓

✓

Total USB ports

2

2

2

2

2

Accessories / cable options

Adult accessories kit¹

A01

●

●

●

●

●

Accessories not included²

A02

●

●

●

●

●

Pediatric accessories kit³

A03

●

●

●

●

●

Neonatal accessories kits⁴

A04

●

●

●

●

●

3 and 5-lead ECG sets

B06

✓

✓

✓

✓

✓

10-lead ECG set

B07

●

●

●

●

●

Measurement parameter options

Philips ST analysis

✓

✓

✓

✓

✓

Impedance respiration

✓

✓

✓

✓

✓

Philips SpO₂⁵

B01

●

●

●

●

●

Masimo SET⁶

B02

●

●

●

●

●

Masimo rainbow[®] SpHb[®]/SpOC^{TM7}

B03

●

●

●

●

●

Masimo rainbow[®] SpCO^{®7}

B04

●

●

●

●

●

Masimo rainbow[®] RRA^{TM7}

B05

●

●

●

●

●

✓ Standard • Optional

Model		CM10	CM12	CM100	CM120	CM150
Measurement parameter options						
Philips NBP	B08	✓	✓	✓	✓	✓
Dual continuous temp	B09	✓	✓	✓	✓	✓
Dual IBP including overlapping IBP display software ⁸	B10	•	•	•	•	•
etCO ₂ Oridion® Microstream® ⁹	B20	•	•	•	•	•
etCO ₂ Respironics CAPNOSTAT® Mainstream ⁹	B21	•	•	•	•	•
Cardiac output ¹⁰	B30		•		•	•
Software options						
Philips basic arrhythmia		✓	✓	✓	✓	✓
Philips enhanced arrhythmia	C01	•	•	•	•	•
Maximum number of waveforms displayed		8	12	8	8	12
Display mini trend, 8 hours	C03		✓		✓	✓
Assisting venous puncture	C04	•	•	•	•	
Night mode	C07	✓	✓	✓	✓	✓
Barcode reader support ¹¹	C08	•	•	•	•	•
ECG filter frequency ¹²	C09	•	•	•	•	•
Philips ST Map ¹³	C10		•		✓	✓
Overlapping IBP display with Dual IBP option ¹²	C12	•	•	•	•	•
Dashboard connectivity	C14	✓	✓	✓	✓	✓
Full disclosure (all waveforms) ¹⁴	C15	•	•	•	•	•
HL7 output	C20	•	•	✓	✓	✓
Hardware and battery options						
Touch screen	E01	•	•	✓	✓	✓
ECG output	E03	✓	✓	✓	✓	✓
Dual speaker	E04			✓	✓	✓
10 inch display size	E05	✓		✓		
12 inch display size	E06		✓		✓	
15 inch display size	E07					✓
Internal recorder	E10	•	•	•	•	•
3 cell lithium ion battery	E11	✓ ²	✓ ²			
9 cell lithium ion battery	E12	•	•	✓ ²	✓ ²	✓ ²
Dual 3 cell lithium ion batteries	E13		• ¹³			
Dual 9 cell lithium ion batteries	E14		• ¹³		•	•
Bed rail hook	E16	•	•	•	•	
Dual battery support	E17		• ¹³		✓	✓
Wireless LAN connectivity	E20	•	•	•	•	•

All monitors supplied with battery (one or two, depending on model and options selected); local power cord; Instructions for Use and Quick card; ECG trunk cable; service guide (on CD); bed rail hook (if ordered); recorder paper (if recorder (E10) is ordered)

¹ Efficia SpO₂ sensor, adult finger (> 50 kg, 110 lbs), 3.0 m (10 ft) cable; Efficia combined one-piece trunk cable/3-lead set, grabber, 2.5 m, (8 ft), AAMI or IEC; Value Care cuff, adult (27 to 35 cm, 10.5 to 14 in.) and Efficia NIBP hose, adult/pediatric, 3.0 m (10 ft)

² Included by default

³ Efficia SpO₂ sensor, pediatric finger (15 to 50 kg, 33 to 110 lbs), 1.5 m (5 ft) cable; Efficia combined one-piece trunk cable/3-lead set, grabber, 2.5 m, (8 ft), AAMI or IEC; Value Care cuff, pediatric (14 to 21.5 cm, 5.5 to 8.5 in.) and Efficia NIBP hose, adult/pediatric, 3.0 m (10 ft)

⁴ Reusable SpO₂ sensor, neonatal, hand/foot; 3 lead ECG trunk cable (AAMI/IEC, 2.7 m, 8.8 ft), preattached ECG electrode, square, metallic leadwire; single-patient NIBP cuff, neonatal (boxes of 40): 3.1 to 5.7 cm (1.2 to 2.2 in.), 4.3 to 8.0 cm (1.7 to 3.1 in.), 5.8 to 10.9 cm (2.3 to 4.3 in.), 7.1 to 13.1 cm (2.8 to 5.2 in.), single-patient NIBP cuff, infant (box of 40): 10.0 to 15.0 cm (3.9 to 5.9 in.), and NIBP hose, neonatal, 3.0 m (10 ft)

⁵ Default unless Masimo selected

⁶ Masimo may not be available in all countries

⁷ Can only be ordered in combination with B02. Only one of B03, B04, or B05 can be ordered

⁸ Automatically also adds C09 and C12

⁹ Only one of B20 or B21 can be ordered

¹⁰ Can only be ordered in combination with B10

¹¹ Barcode reader support is standard on all models but requires the reader hardware option

¹² Added as standard when ordering B10. Can only be ordered in combination with B10

¹³ Can only be ordered in combination with E01

¹⁴ Includes SD card

